

# M610

Dual Camera Image Processor









Homeland Security & Defense



Industrial and Healthcare Manufacturing



are L

Labs and Education



The IST-Quadtek Calico II system from Mirion introduces new features and capabilities designed to enhance the ability to monitor and control our customers processes. The M610 provides precise temperature measurement across the entire screen, by employing innovative lens vignetting correction which is designed to eliminate erroneous temperature measurements at the edge of the image.

The systems flexibility allows one or two video cameras, each with a patented pyrometer, to be displayed through one M610 processor. The M610 sends the collective output to one or two VGA monitors giving the operators the ability to observe process conditions from two locations while measuring up to 32 'free form' temperature measurement zones including virtually any object or region in each field of view.

## **BENEFITS**

- Optimize lower furnace operation of recovery boiler
- · Maintain proper bed profile in recovery boiler
- Reduced hardware costs
- Reduced space and power requirements
- Improved dependability

## **KEY FEATURES**

- 32 'free form' temperature measurement zones which are moveable and sizeable and can be colorized for grouping/clarity
- ndependent emissivity setting for each TMZ
- One or two cameras into one processor
- Continuous clear, real-time video
- Dynamic and easy user interface
- Charting and graphing capability
- Colorization and contrast expansion
- 16 channels 4-20mA output
- Multiple temperature trending capabilities
- Snapshot feature can store images on an automatic or manual basis
- 10 x digital zoom with pan capability
- Connectivity with plant control system
- Large font support for 'viewing at a distance'

**Imaging Systems** 

## SPECIFICATIONS AND PERFORMANCE

Power	100 ~ 240 Vac; 50/60Hz	
Power Consumption	300W max	
Dimensions	176mm (H) x 432mm (W) x 517mm (D) (6.93" x 17" x 20") (Excludes mounting lugs/handles)	
Temperature Range	0° ~ 40°C (32° ~ 104°F)	
Relative Humidity	80% up to 31°C (88°F) decreasing linearly to 50% at 40°C (122°F)	
Video Signal Input	2 x composite video with multiplexed pyrometer data, compatible with Quadtek M300 Series camera	
Video Outputs	DVI with VGA adapters supplied	
Analog Outputs	4 ~ 20mA; 16 programmable channels	
Camera Requirements	M330 and M340 Series IST-Quadtek Spyrometer	
Ancillary Hardware	1 mouse; 1 standard keyboard; 1 DVD-RW drive	
Additional Interfaces	1 serial port; 1 parallel port; 2 network; 4 USB on rear; 2 USB on the front (protected); audio out	
Weight	17.3Kg (38lbs)	



### > UK - FARNBOROUGH

Mirion Technologies, Ltd 2 Columbus Drive, Farnborough, Hampshire, GU14 0NZ

T: +44 1252 375137 | F: +44 1252 391890 | E: quadtek.sales@mirion.com

## > USA - OHIO

Mirion Technologies (IST) Corporation 12954 Stonecreek Drive, Suite C, Pickerington, OH 43147 T: +1 614 367 2050 | F: +1 614 367 2464 | E: isdquadtekusa@mirion.com

## > USA - WASHINGTON

Mirion Technologies (IST) Corporation 19501-144th Ave NE, Suite C400, Woodinville, WA98072 T: +1 425 487 3385 | F: +1 425 487 3375 | E: isdquadtekusa@mirion.com

## > GERMANY - BONN

Mirion Technologies Kaiser-Konrad-Str 93a, D53225, Bonn T: +49 228 625088 | F: +49 228 626 300 | E: rees.sales@mirion.com Please contact your Mirion Technologies representative to advise any specific vibration or seismic qualification.

Copyright © 2014 Mirion Technologies, Inc. or its affiliates. All rights reserved. Mirion, the Mirion logo, and other trade names of Mirion products listed herein are registered trademarks or trademarks of Mirion Technologies, Inc. or its affiliates in the United States and other countries. Third party trademarks mentioned are the property of their respective owners. Specifications may vary according to system configuration. We reserve the right to modify or amend the information herein without prior warning.

The management system governing the manufacture of this product is ISO 9001:2008 certified.



www.mirion.com



# M560

High Temperature Solid State IR Camera





Power



Security & Defense







Healthcare



Industrial and Manufacturing

Labs and Education

# **OVERVIEW**

The IST-Quadtek M560 High Temperature Camera from Mirion is a remote observation system which utilizes a solid state IR device to monitor the smeltbed in recovery boilers, monitor slag build-up in utility power boilers and monitor product distribution and control, as well as burn efficiency in industrial process furnaces. The wavelength selections in conjunction with our special filtering result in:

- Improved image quality
- Ability to view further in typical applications
- Enhanced sensitivity of the overall product insitu

## **KEY FEATURES**

- Solid state IR sensor guarantees no picture degradation or image burn
- Lens tube lengths from 24" to 72" supported
- Medium, wide and superwide lens options
- Small front opening and improved seal reduces air usage and keeps lens cleaner
- Sapphire window more durable and scratch resistant than other than materials
- Minimal preventative maintenance
- Image performance enhancements in typical applications

**Imaging Systems** 


# SPECIFICATIONS AND PERFORMANCE


Camera	
Power Requirements	100/115/230 VAC, 50/60 Hz,24 Watts
Video Output	Monochrome EIA Standard RS-170, 525 lines or CCIR, 625 lines, composite video output and sync; 1.0 to 1.4V p-p


Lens		
Construction	Air-cooled 304 stainless steel outer shroud. Sapphire window for maximum environmental protection	
Lengths	124: L = 550mm/21.7" (503mm/19.8") /136: L = 854mm/33.7" (808mm/31.8") /148: L = 1160mm/45.7" (1113mm/43.8") /160: L = 1465mm/57.7" (1417mm/55.8") /172: L = 1769mm/69.7" (1722mm/67.8")	
Field of View	Medium: 45° horizontal Wide: 70° horizontal Superwide: 90° horizontal	
Diameter	38mm (1.5")	
Optical Filter	Particulate-penetrating proprietary infrared filter	
Cooling Requirements	Instrument-quality air*, 7-10 dm3 s-1 @ 35-70 kPa (15-20 SCFM @ 5-10 psig typical) *Air quality to ISO 8573-1, Class1•7•2	

Enclosure		
Construction	Corrosion-resistant nylon cover; anodized aluminum body; NEMA 4, dust and waterproof	
Cooling Type	Vortex cooled; instrument-quality air; 13 dm3s-1 @ 690kPa (25 SCFM @ 100 psig typical) optional	
Ambient Environment	0° to 60°C (32° to 140°F) operating temperature	

Mechanical		
Focus Adjustment	Optical focus adjustment screw located on back of enclosure	
Video Output Jack	Female PL-259 "UHF" type	
Power Input Jack	Removable waterproof miniplug (JOY type TP, female 3-conductor; mating power cord provided)	
Enclosure Cooling Input	1/4" brass quick-disconnect nipple; mating coupler (Snaptite BVHC4-4F) provided	
Lens Cooling Input	1/2" brass quick-disconnect nipple; mating coupler (Snaptite BVHC8-8F) provided	









#### > USA - NEW YORK

Mirion Technologies (IST) Corporation 315 Daniel Zenker Drive, 200 IST Center, Horseheads, NY 14845 T: +1 607 562 4369 | T: +1 800 432 1478 | F: +1 607 562 4392 | E: isdnuclearusa@mirion.com

## > UK - FARNBOROUGH

Mirion Technologies, Ltd 2 Columbus Drive, Farnborough, Hampshire, GU14 0NZ T: +44 1252 375137 | F: +44 1252 391890 | E: rees.sales@mirion.com

#### > USA - OHIO

Mirion Technologies (IST) Corporation 12954 Stonecreek Drive, Suite C, Pickerington, OH 43147 T: +1 614 367 2050 | F: +1 614 367 2464 | E: isdquadtekusa@mirion.com

## > GERMANY - BONN

Mirion Technologies

Kaiser-Konrad-Str 93a, D53225, Bonn
T: +49 228 625088 | F: +49 228 626 300 | E: rees.sales@mirion.com

Please contact your Mirion Technologies representative to advise any specific vibration or seismic qualification.

Copyright © 2014 Mirion Technologies, Inc. or its affiliates. All rights reserved. Mirion, the Mirion logo, and other trade names of Mirion products listed herein are registered trademarks or trademarks of Mirion Technologies, Inc. or its affiliates in the United States and other countries. Third party trademarks mentioned are the property of their respective owners. Specifications may vary according to system configuration. We reserve the right to modify or amend the information herein without prior warning.

The management system governing the manufacture of this product is ISO 9001:2008 certified.



www.mirion.com 08/14